



Carbide Hole Cutter, 7/8-Inch



This carbide hole cutter cuts quick, precise holes in a variety of materials. Integrated flange prevents the operator from drilling beyond the sheet metal. Split point pilot drill bit prevents bit walking.

Specifications

Application:	Cut Holes in Stainless Steel, Mild Steel, Iron, Copper, and Brass	Hole Diameter:	7/8" (2.2 cm)
Conduit Sizes:	0.5" (1.3 cm)	Shank Size:	3/8" (1 cm)
Maximum Cutting Depth:	3/16" (0.5 cm)	Weight:	4.8 oz (136.1 g)