



1-1/8-Inch Ship Auger Bit 15-Inch Length



The deep, open-throat design of the Ship Auger bit clears chips for faster, cleaner cuts. The shank is 7/16-Inch hex to fit 1/2-Inch (13 mm) and larger three-jaw chucks. Used for heavy construction and repair work in mines, on docks and bridges as well as electrical work.

Specifications

Bit Diameter:	1-1/8" (29 mm)	Shank Diameter:	0.4"
Twist Length:	15" (38.1 cm)	Overall Length:	18" (45.7 cm)
Weight:	1.8 lb (0.8 kg)		