



Insulated Screwdriver, #2 Phillips, 4-Inch Round Shank



The Klein Tools #2 Insulated Phillips Head Screwdriver provides safe electrical insulation up to 1,000-Volt. This screwdriver features 2 layers of insulation around a steel construction to ensure dielectric protection and impact resistance. Cushion-Grip™ handle ensures excellent torque and comfort.

Specifications

Application:	For Work Near Energized Sources	Special Features:	Flame Retardant and Impact Resistant Handle
Tip Type:	Phillips	Magnetic:	No
Tip Size:	#2	Shank Type:	Round
Shank Length:	4" (10.2 cm)	Material:	Induction Hardened Steel
Insulated:	Yes	Handle Material:	High-Dielectric Plastic
Handle Color:	Black	Overall Length (Inch):	8.313
Overall Length (cm):	21.1	Standard:	IEC 60900 and ASTM F1505
Weight (oz):	3.2	Weight (g):	91