



## Heavy Duty Ratcheting Cutter



Ratchet-action design of this heavy-duty Ratcheting Cutter provides maximum leverage with minimum effort. Forged, heat-treated, shear-type blades cut steel and ACSR. Long steel handles have heavy vinyl grips for comfort and slip-resistance. Blade-advance knob quickly rotates the blade to engage the cable or other material being cut.

### Specifications

<b>Type:</b>	Cable Cutter	<b>Soft Cable Maximum Capacity:</b>	2-1/4" (57.2 mm) Diameter, 750 MCM Diameter, Copper or Aluminum
<b>Steel Cable Maximum Capacity:</b>	1-1/4" (31.8 mm) Diameter ACSR, ACAR, 7/16" (11.1 mm) Diameter Common Guy Strand, 5/8" (15.9 mm) Diameter Steel Wire Rope, 1/2" (12.7 mm) Diameter Steel Rod (C.R.S. SOFT)	<b>Handle Color:</b>	Yellow
<b>Overall Length:</b>	28" (71.1 cm)	<b>Weight:</b>	14.0 lb (6.4 kg)