



Slim-Tip 1000V Insulated Screwdriver, #1 Phillips, 6-Inch Round Shank



Klein Tools' Slim-Tip Insulated Screwdrivers have slim profile tips that allow for greater access into terminal blocks, slim-style breakers, or other tight spaces near energized sources. A bright orange coating of insulation protects from electrical shock, is flame and impact resistant, and sits flush with the tip helping to reduce insulation chipping and cracking. Klein insulated tools exceed the ASTM F1505 standards for insulated tools, and are clearly marked with the official 1000V rating symbol. A must-have for any electrician's tool bag, these screwdrivers are available in 4-Inch and 6-Inch lengths and a variety of tips.

Specifications

Application:	For Work Near Energized Sources	Special Features:	Slim Profile Tip
Tip Type:	Phillips	Magnetic:	No
Tip Size:	#1	Shank Type:	Round
Shank Length:	6" (15.2 cm)	Material:	Steel, Plastic
Insulated:	Yes	Handle Material:	Rubber
Handle Color:	Black	Handle Length (Inch):	4.31
Handle Length (cm):	10.9	Handle Diameter:	1.25" (3.2 cm)
Color Code:	Orange	Overall Length (Inch):	10.31
Overall Length (cm):	26.2	Overall Height (Inch):	1.25
Overall Height (cm):	3.2	Overall Width (Inch):	1.25
Overall Width (cm):	3.2	Standard:	ASTM F-1505-16, IEC 60900:2018
Type:	Slim-Tip Insulated Screwdriver	Weight (oz):	7.5
Weight (g):	213		