



Diagonal Cutting Pliers, Insulated, Heavy-Duty, 8-Inch



These 8-Inch Klein Tools Insulated Heavy-Duty Diagonal-Cutting Pliers have durable molded insulation that is flame retardant, impact resistant and clearly marked with 1000-volt rating. The knives are heavy duty induction hardened steel that can cut ACSR, screws, nails, and most hardened wire. Their high-leverage design allows for them to have 36-percent greater cutting power than other similar plier designs.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length (Inch):	7.98
Overall Length (cm):	20.3	Material:	Induction Hardened Steel
Nose Type:	Tapered	Jaw Length (Inch):	0.83
Jaw Length (cm):	2.1	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.49
Jaw Thickness (cm):	1.2	Cutting Knives:	Standard
Cut Style:	Diagonal-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length (Inch):	4.73	Handle Length (cm):	12
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight (oz):	11.2	Weight (g):	318