



Diagonal Cutting Pliers, Insulated, Heavy-Duty, Angled Head, 8-Inch



These Insulated Heavy-Duty Diagonal-Cutting Pliers have durable molded insulation that is flame retardant, impact resistant and clearly marked with 1000-volt rating. The knives are heavy duty induction hardened steel that can cut ACSR, screws, nails, and most hardened wire. The high-leverage design paired with an angled head allows for increased leverage and the ability to work in confined areas.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length (Inch):	8.24
Overall Length (cm):	20.9	Material:	Induction Hardened Steel
Nose Type:	Angled	Jaw Length (Inch):	0.813
Jaw Length (cm):	2.1	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.46
Jaw Thickness (cm):	1.2	Jaw Capacity (Inch):	1.15
Jaw Capacity (cm):	2.9	Cutting Knives:	Standard
Cut Style:	Diagonal-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length (Inch):	4.9	Handle Length (cm):	12.4
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight (oz):	11.2	Weight (g):	318