



Lineman's Pliers, Heavy-Duty Side Cutting, 7-Inch



These lineman's pliers are made of custom, US-made tool steel and feature combination polished and black-oxide finish plus plastic-dipped handles for comfort and ease of identification. 2000 series knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting and gripping power than other plier designs. Cutting knives are induction hardened for long life. The hot-riveted joint ensures smooth action and no handle wobble. Streamlined design with sure-gripping, cross-hatched knurled jaws. Unique handle tempering helps absorb the "snap" when cutting wire. The head is precision-hardened for on-the-job toughness.

Specifications

Type:	Side Cutting Pliers	Application:	ACSR, Screws, Nails, Most Hardened Wire
Overall Length (Inch):	7.77	Overall Length (cm):	19.7
Material:	Steel	Nose Type:	New England
Jaw Length (Inch):	1.284	Jaw Length (cm):	3.3
Jaw Width (Inch):	1.03	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.53	Jaw Thickness (cm):	1.3
Jaw Capacity (Inch):	1.42	Jaw Capacity (cm):	3.6
Knife Length (Inch):	0.75	Knife Length (cm):	1.9
Cut Style:	Cross Cut	Joint Type:	Hot Riveted
Handle Color:	Light Blue	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	4.52	Handle Length (cm):	11.5
Insulated:	No	Tether Capable:	No
Weight (oz):	10.6	Weight (g):	301