



Lineman's Pliers, Heavy-Duty Side Cutting, 8-Inch



These lineman's pliers are made of custom, US-made tool steel and feature combination polished and black-oxide finish plus plastic-dipped handles for comfort and ease of identification. 2000 series knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting and gripping power than other plier designs. Cutting knives are induction hardened for long life. The hot-riveted joint ensures smooth action and no handle wobble. Streamlined design with sure-gripping, cross-hatched knurled jaws. Unique handle tempering helps absorb the "snap" when cutting wire. The head is precision-hardened for on-the-job toughness.

Specifications

Type:	Side Cutting Pliers	Application:	ACSR, Screws, Nails, Most Hardened Wire
Overall Length (Inch):	8.59	Overall Length (cm):	21.8
Material:	Steel	Nose Type:	New England
Jaw Length (Inch):	1.44	Jaw Length (cm):	3.7
Jaw Width (Inch):	1.109	Jaw Width (cm):	2.8
Jaw Thickness (Inch):	0.6	Jaw Thickness (cm):	1.5
Jaw Capacity (Inch):	1.58	Jaw Capacity (cm):	4
Knife Length (Inch):	0.719	Knife Length (cm):	1.8
Cut Style:	Cross Cut	Joint Type:	Hot Riveted
Handle Color:	Light Blue	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	4.84	Handle Length (cm):	12.3
Insulated:	No	Tether Capable:	No
Weight (oz):	13.6	Weight (g):	386