



Lineman's Pliers with Crimping, 9-Inch



These Lineman's Pliers feature a built-in crimper for non-insulated connectors. Heavy-duty cutting knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting power. The dual-material Journeyman handles are more comfortable and durable than other handles.

Specifications

Type:	Heavy Duty High Leverage Crimping Pliers	Application:	ACSR, Screws, Nails, Most Hardened Wire
Overall Length (Inch):	9.35	Overall Length (cm):	23.7
Material:	Steel	Nose Type:	New England
Jaw Length (Inch):	1.594	Jaw Length (cm):	4
Jaw Width (Inch):	1.25	Jaw Width (cm):	3.2
Jaw Thickness (Inch):	0.625	Jaw Thickness (cm):	1.6
Jaw Capacity (Inch):	1.375	Jaw Capacity (cm):	3.5
Knife Length (Inch):	0.781	Knife Length (cm):	2
Joint Type:	Hot Riveted	Handle Color:	Light Blue
Handle Finish:	Plastic-Dipped	Handle Length (Inch):	5.41
Handle Length (cm):	13.7	Insulated:	No
Tether Capable:	No	Weight (oz):	17.6
Weight (g):	499		