



Lineman's Pliers, Bolt Thread-Holding



These Lineman's Side-Cutting pliers feature a hinge opening to hold and clean 5/8" (16 mm) pole line and hardware bolts or threaded rods. Cutting knives are induction hardened for long life. The 2000 series blades are designed for heavy-duty cutting of ACSR, screws, nails, and most hardened wire. The high-leverage design provides 46-Percent greater cutting power than other plier designs. Exclusive handle tempering absorbs the snap when cutting wire. Pick up these Klein's and feel the difference.

Specifications

Type:	Side Cutting Pliers	Application:	Holds 5/8" (1.6 cm) Pole Line and Hardware Bolts, Threaded Rods; Cuts ACSR, Screws, Nails, and Most Hardened Wire
Overall Length (Inch):	9.35	Overall Length (cm):	23.7
Overall Height (Inch):	0.75	Overall Height (cm):	1.9
Overall Width (Inch):	2.06	Overall Width (cm):	5.2
Material:	Steel	Nose Type:	New England
Jaw Length (Inch):	1.594	Jaw Length (cm):	4
Jaw Width (Inch):	1.25	Jaw Width (cm):	3.2
Jaw Thickness (Inch):	0.625	Jaw Thickness (cm):	1.6
Jaw Capacity (Inch):	1.43	Jaw Capacity (cm):	3.6
Knife Length (Inch):	0.781	Knife Length (cm):	2
Joint Type:	Hot Riveted	Handle Color:	Light Blue
Handle Finish:	Plastic-Dipped	Handle Length (Inch):	5.41
Handle Length (cm):	13.7	Insulated:	No
Tether Capable:	No	Weight (oz):	19.2
Weight (g):	544		