



Pliers, Long Nose Side-Cutters, Insulated, 7-Inch



Klein Tools Insulated Long Nose Side-Cutting pliers are 1000V rated for safety on the job. The long nose is designed for grabbing and looping wire. Dual layer, orange-over-white insulation provides a warning sign that insulation may be compromised. The molded insulation meets or exceeds ASTM F1505-16 and IEC 60900:2012 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length (Inch):	7.37
Overall Length (cm):	18.7	Material:	Induction Hardened Steel
Jaw Length (Inch):	2.43	Jaw Length (cm):	6.2
Jaw Width (Inch):	0.688	Jaw Width (cm):	1.7
Jaw Thickness (Inch):	0.375	Jaw Thickness (cm):	1
Point Diameter (Inch):	0.094	Point Diameter (cm):	0.2
Cutting Knives:	Standard	Knife Length (Inch):	0.572
Knife Length (cm):	1.5	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length (Inch):	3.87
Handle Length (cm):	9.8	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight (oz):	4.8
Weight (g):	136		