



Pliers, Needle Nose Side-Cutters with Spring, 7-Inch



These Long-Nose Side-Cutters are spring-loaded for self-opening. The cutting knives are induction hardened for maximum life. Made of forged steel for durability with a long nose for grabbing and looping wire.

Specifications

Type:	Long Nose Side Cutting Pliers	Overall Length (Inch):	7.17
Overall Length (cm):	18.2	Jaw Length (Inch):	2.43
Jaw Length (cm):	6.2	Jaw Width (Inch):	0.688
Jaw Width (cm):	1.7	Jaw Thickness (Inch):	0.375
Jaw Thickness (cm):	1	Point Diameter (Inch):	0.094
Point Diameter (cm):	0.2	Knife Length (Inch):	0.572
Knife Length (cm):	1.5	Handle Color:	Yellow
Handle Finish:	Plastic-Dipped	Handle Length (Inch):	3.54
Handle Length (cm):	9	Insulated:	No
Weight (oz):	4.6	Weight (g):	130