



Long Nose Pliers, Insulated, 8-Inch



Klein Tools Insulated Long Nose Side-Cutting pliers are 1000V rated for safety on the job. The long nose is designed to grab and loop wire. Dual layer, orange-over-white insulation provides a warning sign that insulation may be compromised. The molded insulation meets or exceeds ASTM F1505-16 and IEC 60900:2012 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length (Inch):	8.91
Overall Length (cm):	22.6	Material:	Induction Hardened Steel
Jaw Length (Inch):	2.32	Jaw Length (cm):	5.9
Jaw Width (Inch):	1.02	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.5	Jaw Thickness (cm):	1.3
Point Diameter (Inch):	0.125	Point Diameter (cm):	0.3
Cutting Knives:	Standard	Knife Length (Inch):	0.693
Knife Length (cm):	1.8	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length (Inch):	4.79
Handle Length (cm):	12.2	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight (oz):	11.2
Weight (g):	318		