



Insulated Long Nose Pliers, Side-Cutting/Stripping



These Klein Tools long nose side-cutting/stripping pliers are made of forged steel for maximum durability. They have a heavier design and extended handles to improve leverage and power. And they have two layer bright orange insulation that is both flame retardant and provide electric protection for up to 1000 V.

Specifications

Type:	Long Nose	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length (Inch):	8.91
Overall Length (cm):	22.6	Material:	Induction Hardened Steel
Jaw Length (Inch):	2.32	Jaw Length (cm):	5.9
Jaw Width (Inch):	1.02	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.5	Jaw Thickness (cm):	1.3
Jaw Capacity (Inch):	2.36	Jaw Capacity (cm):	6
Point Diameter (Inch):	0.125	Point Diameter (cm):	0.3
Cutting Knives:	Standard	Knife Length (Inch):	0.693
Knife Length (cm):	1.8	Cut Style:	Side-Cutting and Skinning
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length (Inch):	4.79
Handle Length (cm):	12.2	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight (oz):	11.2
Weight (g):	318		