



Pliers, Needle Nose Side Cutters with Stripping, 8-Inch



These Long Nose, Side-Cutters strip 12 AWG solid wire while the heavier design provides more cutting power. The cutting knives are induction hardened for maximum life. The long nose is great for grabbing and looping wire.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	Side Cutting; Stripping
Overall Length (Inch):	8.41	Overall Length (cm):	21.4
Jaw Length (Inch):	2.32	Jaw Length (cm):	5.9
Jaw Width (Inch):	1.02	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.5	Jaw Thickness (cm):	1.3
Jaw Capacity (Inch):	2.36	Jaw Capacity (cm):	6
Point Diameter (Inch):	0.125	Point Diameter (cm):	0.3
Knife Length (Inch):	0.693	Knife Length (cm):	1.8
Handle Color:	Yellow	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	4.03	Handle Length (cm):	10.2
Insulated:	No	Weight (oz):	9.4
Weight (g):	266		