



Pliers, Needle Nose Side Cutters with Stripping and Crimping, 8-Inch



These Long Nose Side-Cutting Pliers strip 12 AWG solid wire and crimp connectors, lugs and terminals. The heavier design allows for easier, more comfortable cutting. The cutting knives are induction hardened for long life. The long nose is great for grabbing and looping wire.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	Side Cutting; Stripping; Crimping
Overall Length (Inch):	8.41	Overall Length (cm):	21.4
Jaw Length (Inch):	2.32	Jaw Length (cm):	5.9
Jaw Width (Inch):	1.02	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.5	Jaw Thickness (cm):	1.3
Point Diameter (Inch):	0.125	Point Diameter (cm):	0.3
Knife Length (Inch):	0.693	Knife Length (cm):	1.8
Handle Color:	Yellow	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	4.03	Handle Length (cm):	10.2
Insulated:	No	Weight (oz):	9.8
Weight (g):	278	Crimps:	Yes