



Lineman's Square Nose Pliers, 9-Inch



These High-Leverage, Side-Cutting Pliers feature a square nose for twisting and grabbing wires. The rivet is closer to the cutting edge for 46-Percent more cutting and gripping power than other pliers. Induction hardened cutting knives are extra durable for longer life. The exclusive handle tempering absorbs the snap when cutting wire. Forged from custom US-made steel for maximum durability.

Specifications

Type:	Side Cutting Pliers	Application:	#8 AWG Copper, Aluminum and Other Soft Metals
Overall Length:	9.35" (23.7 cm)	Overall Width:	2.06" (5.2 cm)
Material:	Induction Hardened Steel	Nose Type:	Square
Jaw Length:	1.91" (4.9 cm)	Jaw Width:	1.24" (3.1 cm)
Jaw Thickness:	0.62" (1.6 cm)	Jaw Capacity:	1.375" (3.5 cm)
Cutting Knives:	1	Knife Length:	0.781" (2 cm)
Cut Style:	Side-Cutting	Screw Shearing:	No
Joint Type:	Hot-Riveted	Handle Color:	Dark Blue
Handle Finish:	Plastic-Dipped	Handle Length:	5.41" (13.7 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.0 lb (0.5 kg)		