



Lineman's Crimping Pliers, 9-Inch



The Lineman's Crimping Pliers feature a crimping die behind the hinge. This provides superior leverage when crimping non-insulated connectors, lugs, and terminals. The rivet on these pliers are closer to the cutting edge which provides 46-Percent more cutting and gripping power than other pliers. Induction hardened cutting knives are extra durable for longer life.

Specifications

Type:	High Leverage Side Cutting/Connector Crimping Pliers	Application:	#8 AWG Copper, Aluminum and Other Soft Metals and Crimps Non-insulated Connectors, Lugs, and Terminals
Special Features:	Crimper	Overall Length (Inch):	9.35
Overall Length (cm):	23.7	Overall Width (Inch):	2.06
Overall Width (cm):	5.2	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length (Inch):	1.91
Jaw Length (cm):	4.9	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.62
Jaw Thickness (cm):	1.6	Jaw Capacity (Inch):	1.375
Jaw Capacity (cm):	3.5	Cutting Knives:	1
Knife Length (Inch):	0.781	Knife Length (cm):	2
Cut Style:	Side-Cutting	Screw Shearing:	No
Joint Type:	Hot-Riveted	Handle Color:	Yellow
Handle Finish:	Plastic-Dipped	Handle Length (Inch):	5.41
Handle Length (cm):	13.7	Insulated:	No
Tether Capable:	No	Weight (oz):	16
Weight (g):	454		