



Side Cutting Pliers, New England Insulated, 9-Inch



These Klein Tools Side Cutting New England Insulated Pliers are insulated by two layers and pass both the IEC 60900 and ASTM F1505 standards. They are made of forged steel with induction-hardened knives for strength and durability. And they have high-leverage design which provides 46-percent more cutting and gripping power than other plier designs.

Specifications

Type:	Side Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wires
Special Features:	Integral Guards Help Prevent Hand Contact With Conductive Parts	Overall Length (Inch):	9.68
Overall Length (cm):	24.6	Overall Width (Inch):	2.49
Overall Width (cm):	6.3	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length (Inch):	1.91
Jaw Length (cm):	4.9	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.62
Jaw Thickness (cm):	1.6	Jaw Capacity (Inch):	1.375
Jaw Capacity (cm):	3.5	Cutting Knives:	1
Knife Length (Inch):	0.781	Knife Length (cm):	2
Cut Style:	Side-Cutting	Screw Shearing:	No
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length (Inch):	5.73
Handle Length (cm):	14.6	Insulated:	Yes
Tether Capable:	No	Standards:	IEC 60900 and ASTM F1505
Weight (oz):	20	Weight (g):	567