



## Lineman's Bolt-Thread Holding Pliers, 9-Inch



The hinge opening on Klein's Lineman's Bolt-Thread Holding Pliers holds and cleans 5/8" (16 mm) pole line and hardware bolts or threaded rods. The plier head is precision-hardened for on-the-job toughness. The exclusive handle tempering helps absorb the "snap" when cutting wire helping reduce fatigue.

### Specifications

<b>Type:</b>	Side Cutting Pliers	<b>Application:</b>	Core High Leverage Side Cutting Features Plus: 5/8" (1.59 mm) Pole Line and Hardware Bolts, Threaded Rods
<b>Overall Length (Inch):</b>	9.35	<b>Overall Length (cm):</b>	23.7
<b>Overall Height (Inch):</b>	0.75	<b>Overall Height (cm):</b>	1.9
<b>Overall Width (Inch):</b>	2.06	<b>Overall Width (cm):</b>	5.2
<b>Material:</b>	Induction Hardened Steel	<b>Nose Type:</b>	New England
<b>Jaw Length (Inch):</b>	1.91	<b>Jaw Length (cm):</b>	4.9
<b>Jaw Width (Inch):</b>	1.25	<b>Jaw Width (cm):</b>	3.2
<b>Jaw Thickness (Inch):</b>	0.62	<b>Jaw Thickness (cm):</b>	1.6
<b>Jaw Capacity (Inch):</b>	1.375	<b>Jaw Capacity (cm):</b>	3.5
<b>Cutting Knives:</b>	1	<b>Knife Length (Inch):</b>	0.797
<b>Knife Length (cm):</b>	2	<b>Cut Style:</b>	Side-Cutting
<b>Screw Shearing:</b>	No	<b>Joint Type:</b>	Hot-Riveted
<b>Handle Color:</b>	Dark Blue	<b>Handle Finish:</b>	Plastic-Dipped
<b>Handle Length (Inch):</b>	5.41	<b>Handle Length (cm):</b>	13.7
<b>Insulated:</b>	No	<b>Tether Capable:</b>	No
<b>Weight (oz):</b>	17.6	<b>Weight (g):</b>	499