



High-Leverage Ironworker's Pliers



These Klein Tools High-Leverage Ironworker's Pliers have induction hardened side-cutting knives for improved durability and a longer lifespan. They have heavy duty knurled jaws and a spring-loaded self-opening on hot-riveted joint for smooth, easy, and powerful action. The high-leverage design with handform handles and the rivet being closer to the cutting edge allows for 46 percent more cutting and gripping power.

Specifications

Type:	Ironworker's Pliers	Application:	Used for Rebar, High Leverage
Special Features:	Spring Loaded	Overall Length (Inch):	9.35
Overall Length (cm):	23.7	Overall Width (Inch):	2.06
Overall Width (cm):	5.2	Material:	Induction Hardened Steel
Nose Type:	Square	Jaw Length (Inch):	1.91
Jaw Length (cm):	4.9	Jaw Width (Inch):	1.24
Jaw Width (cm):	3.1	Jaw Thickness (Inch):	0.62
Jaw Thickness (cm):	1.6	Jaw Capacity (Inch):	1.375
Jaw Capacity (cm):	3.5	Cutting Knives:	1
Knife Length (Inch):	0.781	Knife Length (cm):	2
Cut Style:	Side-Cutting	Screw Shearing:	No
Joint Type:	Hot-Riveted	Handle Color:	Blue
Handle Finish:	Plastic-Dipped	Handle Length (Inch):	5.41
Handle Length (cm):	13.7	Insulated:	No
Tether Capable:	No	Weight (oz):	16
Weight (g):	454		