



## Diagonal Cutting Pliers, Insulated, 7-Inch



These Insulated Diagonal-Cutting pliers have dual layered grips that are flame retardant, impact resistant, and rated for 1000-volts. They feature a tapered nose design with induction hardened cutting knives for durability. They are made of forged steel and have a hot-riveted joint for smooth action and no handle wobble.

### Specifications

<b>Type:</b>	Diagonal Cutting Pliers	<b>Special Features:</b>	Flame Retardant and Impact Resistant Handle
<b>Overall Length (Inch):</b>	7.67	<b>Overall Length (cm):</b>	19.5
<b>Material:</b>	Induction Hardened Steel	<b>Nose Type:</b>	Tapered
<b>Jaw Length (Inch):</b>	1	<b>Jaw Length (cm):</b>	2.5
<b>Jaw Width (Inch):</b>	0.969	<b>Jaw Width (cm):</b>	2.5
<b>Jaw Thickness (Inch):</b>	0.5	<b>Jaw Thickness (cm):</b>	1.3
<b>Jaw Capacity (Inch):</b>	1.1	<b>Jaw Capacity (cm):</b>	2.8
<b>Cutting Knives:</b>	Standard	<b>Cut Style:</b>	Diagonal-Cutting
<b>Joint Type:</b>	Hot-Riveted	<b>Handle Color:</b>	Orange
<b>Handle Finish:</b>	2-Layer Insulation	<b>Handle Length (Inch):</b>	4.34
<b>Handle Length (cm):</b>	11	<b>Insulated:</b>	Yes
<b>Standard:</b>	IEC 60900 and ASTM F1505	<b>Weight (oz):</b>	11.2
<b>Weight (g):</b>	318		