



## Diagonal Cutting Pliers, Insulated, High Leverage, 8-Inch



These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life.

### Specifications

<b>Type:</b>	Diagonal Cutting Pliers	<b>Application:</b>	ACSR, Screws, Nails and Most Hardened Wire
<b>Special Features:</b>	Flame Retardant and Impact Resistant Handle	<b>Overall Length (Inch):</b>	8.24
<b>Overall Length (cm):</b>	20.9	<b>Material:</b>	Induction Hardened Steel
<b>Nose Type:</b>	Tapered	<b>Jaw Length (Inch):</b>	0.781
<b>Jaw Length (cm):</b>	2	<b>Jaw Width (Inch):</b>	1.25
<b>Jaw Width (cm):</b>	3.2	<b>Jaw Thickness (Inch):</b>	0.46
<b>Jaw Thickness (cm):</b>	1.2	<b>Cutting Knives:</b>	Standard
<b>Cut Style:</b>	Diagonal-Cutting	<b>Joint Type:</b>	Hot-Riveted
<b>Handle Color:</b>	Orange	<b>Handle Finish:</b>	2-Layer Insulation
<b>Handle Length (Inch):</b>	4.9	<b>Handle Length (cm):</b>	12.4
<b>Insulated:</b>	Yes	<b>Standard:</b>	IEC 60900 and ASTM F1505
<b>Weight (oz):</b>	11.2	<b>Weight (g):</b>	318