



Ironworker's Diagonal Cutting Pliers, High-Leverage, 9-Inch



These diagonal-cutting pliers were designed for rebar work, and are popular with Ironworkers. The 13 degree angled head makes it easier to work in confined spaces while the hooked handle improves the grip and reduces slippage. The high-leverage design has 36-Percent more cutting power. A hot-riveted joint ensures smooth action and no wobble in the handle. This pair will be your go-to tool when working with soft annealed rebar tie wire.

Specifications

Type:	Ironworker's Pliers	Application:	Soft Annealed Rebar Tie Wire
Overall Length (Inch):	9.13	Overall Length (cm):	23.2
Overall Height (Inch):	2	Overall Height (cm):	5.1
Material:	Steel	Jaw Length (Inch):	0.813
Jaw Length (cm):	2.1	Jaw Width (Inch):	1.188
Jaw Width (cm):	3	Jaw Thickness (Inch):	0.46
Jaw Thickness (cm):	1.2	Jaw Capacity (Inch):	1
Jaw Capacity (cm):	2.5	Cutting Knives:	Standard
Cut Style:	Standard	Joint Type:	Hot Riveted
Handle Color:	Red	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	5.88	Handle Length (cm):	14.9
Insulated:	No	Tether Capable:	No
Standard:	Yes	Weight (oz):	10.9
Weight (g):	309		