



Pliers, Standard Needle Nose Pliers, Spring-Loaded, 6-Inch



These Long-Nose pliers are spring-loaded for self-opening action. The slim head design works well in confined areas. Jaws are knurled for sure wrapping and looping of wire. Curved handles provide greater tool control while the joint is hot-riveted for smooth action and no handle wobble. Made of the finest U.S. steel alloy, they are forged, precision machined, hardened, and carefully tempered for maximum strength.

Specifications

Type:	Long Nose Pliers	Overall Length:	6.68" (17 cm)
Jaw Length:	1.895" (4.8 cm)	Jaw Width:	0.688" (1.7 cm)
Jaw Thickness:	0.375" (1 cm)	Jaw Capacity:	1.75" (4.5 cm)
Point Diameter:	0.094" (0.24 cm)	Handle Color:	Yellow
Handle Finish:	Plastic-Dipped	Handle Length:	3.43" (8.7 cm)
Weight:	4.5 oz (127 g)		