



Lineman's Pliers Bolt Thread-Holding, 9-Inch



The hinge opening on these Lineman's Pliers holds and cleans 5/8-Inch (16 mm) pole line and hardware bolts or threaded rods. Thicker, dipped handles are more comfortable and easier to grab with gloved hands. They are forged, precision machined, hardened, and carefully tempered for maximum strength. Klein pliers provide exceptional performance and durability.

Specifications

Type:	Side Cutting Pliers	Application:	Core High Leverage Side Cutting Features Plus: 5/8" (15.9 mm) Pole Line and Hardware Bolts, Threaded Rods
Special Features:	Oversized	Overall Length (Inch):	9.35
Overall Length (cm):	23.7	Overall Width (Inch):	2.06
Overall Width (cm):	5.2	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length (Inch):	1.91
Jaw Length (cm):	4.9	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.62
Jaw Thickness (cm):	1.6	Jaw Capacity (Inch):	1.375
Jaw Capacity (cm):	3.5	Cutting Knives:	1
Knife Length (Inch):	0.781	Knife Length (cm):	2
Cut Style:	Side-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Light Red	Handle Finish:	Heavy Plastic-Dipped
Handle Length (Inch):	5.41	Handle Length (cm):	13.7
Insulated:	No	Tether Capable:	Yes
Weight (oz):	19.2	Weight (g):	544