



Journeyman Universal Combination Pliers



These 8-Inch Universal High-Leverage Combination Pliers feature a crimping die behind the hinge for superior leverage while crimping non-insulated connectors, lugs and terminals and a high-leverage design, with the rivet closer to the cutting edge for 40-Percent greater cutting and gripping power than other pliers designs. The universal tapered head-design allows for greater access in confined spaces. Klein's trademark dual-material Journeyman handles feature a soft outer surface for comfort and a hard inner material for toughness and durability.

Specifications

Type:	Journeyman Combination Pliers	Application:	Noninsulated Connectors, Lugs, and Terminals
Overall Length (Inch):	8.78	Overall Length (cm):	22.3
Material:	Steel	Nose Type:	Universal
Jaw Length (Inch):	1.78	Jaw Length (cm):	4.5
Jaw Width (Inch):	1.02	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.55	Jaw Thickness (cm):	1.4
Jaw Capacity (Inch):	2.125	Jaw Capacity (cm):	5.4
Knife Length (Inch):	0.711	Knife Length (cm):	1.8
Handle Color:	Dark Blue/Black	Handle Finish:	Journeyman™ Dual Material
Handle Length (Inch):	5.1	Handle Length (cm):	13
Insulated:	No	Tether Capable:	No
Weight (oz):	13.1	Weight (g):	371