



Pliers, Needle Nose Side-Cutters, Stripping, 8-Inch



These Long Nose Side-Cutters strip 12 AWG solid insulated wire. The slim head easily gets into confined areas while the extended handles provide added reach and leverage. Innovative dual material Journeyman™ grips are more comfortable and last longer than other handles. The heavy-duty design allows for easier, more comfortable cutting.

Specifications

Type:	Long Nose Pliers	Application:	Strips 12 AWG Wires
Overall Length (Inch):	8.42	Overall Length (cm):	21.4
Jaw Length (Inch):	2.32	Jaw Length (cm):	5.9
Jaw Width (Inch):	1.02	Jaw Width (cm):	2.6
Jaw Thickness (Inch):	0.5	Jaw Thickness (cm):	1.3
Jaw Capacity (Inch):	2.36	Jaw Capacity (cm):	6
Point Diameter (Inch):	0.125	Point Diameter (cm):	0.3
Knife Length (Inch):	0.693	Knife Length (cm):	1.8
Handle Color:	Yellow/Black	Handle Finish:	Journeyman™ Dual-Material
Handle Length (Inch):	4.45	Handle Length (cm):	11.3
Insulated:	No	Weight (oz):	10.2
Weight (g):	289		