



9-Inch Journeyman™ Pliers Side Cutting



These Klein Tools 9-Inch Journeyman pliers are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. Their streamlined design is paired with their cross-hatched knurled jaws for confident gripping. And their unique tempered handle design, with dual material Journeyman handles provide a better grip and absorbs the snap when using their side-cutting capabilities.

Specifications

Type:	Side Cutting Pliers	Application:	General Purpose
Overall Length (Inch):	9.55	Overall Length (cm):	24.3
Overall Height (Inch):	0.75	Overall Height (cm):	1.9
Overall Width (Inch):	2.29	Overall Width (cm):	5.8
Material:	Induction Hardened Steel	Nose Type:	New England
Jaw Length (Inch):	1.91	Jaw Length (cm):	4.9
Jaw Width (Inch):	1.25	Jaw Width (cm):	3.2
Jaw Thickness (Inch):	0.62	Jaw Thickness (cm):	1.6
Jaw Capacity (Inch):	1.375	Jaw Capacity (cm):	3.5
Cutting Knives:	1	Knife Length (Inch):	0.781
Knife Length (cm):	2	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Dark Blue/Black
Handle Finish:	Journeyman™ Dual-Material	Handle Length (Inch):	5.55
Handle Length (cm):	14.1	Insulated:	No
Tether Capable:	No	Weight (oz):	17.6
Weight (g):	499		