



## Journeyman™ Pliers Connector Crimp Side Cut 9-Inch



These Klein Tools Journeyman Pliers Connector Crimp Side Cut, have a high-leverage design, including the crimping die being placed behind the hinge. They are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. They also have cross-hatched knurled jaws and handform handles for better all around grip.

### Specifications

<b>Type:</b>	High Leverage Side Cutting/Connector Crimping Pliers	<b>Application:</b>	Crimps Noninsulated Connectors, Lugs, and Terminals
<b>Special Features:</b>	Crimper	<b>Overall Length (Inch):</b>	9.55
<b>Overall Length (cm):</b>	24.3	<b>Overall Width (Inch):</b>	2.29
<b>Overall Width (cm):</b>	5.8	<b>Material:</b>	Induction Hardened Steel
<b>Nose Type:</b>	New England	<b>Jaw Length (Inch):</b>	1.91
<b>Jaw Length (cm):</b>	4.9	<b>Jaw Width (Inch):</b>	1.25
<b>Jaw Width (cm):</b>	3.2	<b>Jaw Thickness (Inch):</b>	0.62
<b>Jaw Thickness (cm):</b>	1.6	<b>Jaw Capacity (Inch):</b>	1.375
<b>Jaw Capacity (cm):</b>	3.5	<b>Cutting Knives:</b>	1
<b>Knife Length (Inch):</b>	0.797	<b>Knife Length (cm):</b>	2
<b>Cut Style:</b>	Side-Cutting	<b>Screw Shearing:</b>	No
<b>Joint Type:</b>	Hot-Riveted	<b>Handle Color:</b>	Yellow/Black
<b>Handle Finish:</b>	Journeyman™ Dual-Material	<b>Handle Length (Inch):</b>	5.55
<b>Handle Length (cm):</b>	14.1	<b>Insulated:</b>	No
<b>Tether Capable:</b>	No	<b>Weight (oz):</b>	16
<b>Weight (g):</b>	454		