



Hybrid Pliers with Crimper, Fish Tape Puller and Wire Stripper



Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and terminals make this a must-have tool for your bag.

Specifications

Type:	High Leverage Stripping Crimping Shearing Side-Cut Hybrid Plier	Application:	Strip (10-14 SLD)(12-16 STR), Bolt Shear #6-32 and #8-32, Crimps Non-Insulated Connectors, Lugs and Terminals, Cuts Screws, Nails and Most Hardened Wire
Special Features:	High-Leverage Design	Overall Length (Inch):	8.98
Overall Length (cm):	22.8	Overall Height (Inch):	0.75
Overall Height (cm):	1.9	Overall Width (Inch):	2.25
Overall Width (cm):	5.7	Material:	Chrome-Vanadium Steel
Nose Type:	Square	Jaw Length (Inch):	2.04
Jaw Length (cm):	5.2	Jaw Width (Inch):	1.154
Jaw Width (cm):	2.9	Jaw Thickness (Inch):	0.6
Jaw Thickness (cm):	1.5	Jaw Capacity (Inch):	1.5
Jaw Capacity (cm):	3.8	Cutting Knives:	Yes
Knife Length (Inch):	0.8	Knife Length (cm):	2
Cut Style:	Side Cut	Strips and Cuts AWG Solid:	10-14
Strips and Cuts AWG Stranded:	12-16	Screw Shearing:	6-32, 8-32
Joint Type:	Solid	Handle Color:	Gray/Black
Handle Finish:	Journeyman™ Dual Material	Handle Length (Inch):	5.01
Handle Length (cm):	12.7	Insulated:	No
Tether Capable:	No	Weight (oz):	10.9

Weight (g):	309
-------------	-----