

### Features

- Brass construction and valve bodies
- Vandal-resistant laminar outlet
- Quarter-turn washerless ceramic disc valves
- Less drain
- Lever handles
- 5-3/16" (132 mm) gooseneck spout
- 1.0 gal/min (3.8 l/m) maximum flow rate at 60 psi (4.14 bar).

### Installation

- For 8" – 16" (203 – 406 mm) centers



ADA

CSA B651


OBC

### Codes/Standards

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 61  
NSF/ANSI/CAN 372  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Faucet flow rate: 1 gal/min (3.8 l/min)

### Spout:

Spout reach: 5-3/16" (132 mm)

### Notes

Install this product according to the installation guide.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.