

PRODUCT INFORMATION PACKET



Model No: 191545.00

Catalog No: 191545.00

Pedestal Fan Motor, 0.33 HP, 1 Ph, 60 Hz, 115/230 V, 1800 RPM, 48YZ Frame, TEAO



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

| | | | |
|------------------------|----------------|----------------------------|---------------------------|
| Output HP | 0.33 Hp | Output KW | 0.25 kW |
| Frequency | 60 Hz | Voltage | 115/230 V |
| Current | 3.0/1.5 A | Speed | 1755 rpm |
| Service Factor | 1 | Phase | 1 |
| Efficiency | 74 % | Power Factor | 98 |
| Duty | Continuous | Insulation Class | F |
| Design Code | NO DESIGN CODE | KVA Code | D |
| Frame | 48YZ | Enclosure | Totally Enclosed Air Over |
| Thermal Protection | Automatic | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6203 | Opp Drive End Bearing Size | 6203 |
| UL | Recognized | CSA | Y |
| CE | N | IP Code | 55 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|---------------------------|--------------------|------------------------|
| Electrical Type | Permanent Split Capacitor | Starting Method | Across The Line |
| Poles | 4 | Rotation | Selective Clockwise |
| Resistance Main | 14.23 Ohms | Mounting | Round - Extended Studs |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Stainless Steel |
| Shaft Type | Single Special Extension | Overall Length | 11.58 in |
| Shaft Diameter | 0.500 in | Shaft Extension | 4.05 in |
| Assembly/Box Mounting | F1 ONLY | | |
| Outline Drawing | OL19154500 | Connection Drawing | N/A |

