

PRODUCT INFORMATION PACKET

Model No: M1145034.00

Catalog No: M1145034.00

Parallel Shaft Gearmotor, 0.16 HP, 1 Ph, 60/50 Hz, 115 V, 90 RPM, 38 Frame, TEFC



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	0.16 Hp	Output KW	0.12 kW
Frequency	60/50 Hz	Voltage	115 V
Current	2.1/1.1 A	Speed	90 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
KVA Code	D	Frame	38
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	6201
Opp Drive End Bearing Size	6201	UL	Recognized
CSA	Y	CE	Y

Technical Specifications

Rotation	Reversible	Mounting	Special
Shaft Type	Parallel	Overall Length	12.13 in
Frame Length	5.88 in	Shaft Diameter	0.625 in
Shaft Extension	1.5 in	Torque	103 LB-IN
Outline Drawing	M1030381	Connection Drawing	M1005040.02

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2022

