



UPC Code : 078477495629

Country Of Origin : Mexico

M5631-W

Lev-Lok Decora Plus Single-Pole Rocker Switch, Illuminated - Load OFF, Heavy-Duty Industrial Specification Grade, 20 Amp, 120/277 Volt AC, Modular, Self-Grounding - White

Mating Lev-Lok Wiring Module Required for Use

Technical Information

Material Specifications

Actuator Material : Polycarbonate

At Rated Voltage : 1 HP @ 120V, 2HP @ 240V

Base Material : Nylon

Contact Material : Silver-Alloy

Frame Material : Polycarbonate

Ground Clips : Brass

Strap Material : .046" Thick Galvanized Steel

Warranty

Amperage : 20 A

Dielectric Voltage : Withstands 1500 V for 1 minute

Endurance : 30,000 cycles min

Grounding : Self-Grounding

Overload UL20 Test : 100 cycles of OL at 4.8 times rated current

Temperature Rise : Maximum 30° C Rise

Voltage : 120/277 VAC

Warranty : 10-Year Limited

AC Horsepower Rating

At Rated Voltage : 1 HP @ 120V, 2HP @ 240V

Flammability : Rated V-2 per UL 94

Operating Temperature : -40°C to 60°C

Electrical Specifications

Actuator Material : Polycarbonate

Amperage : 20 A

Base Material : Nylon

Dielectric Voltage : Withstands 1500 V for 1 minute

Endurance : 30,000 cycles min

Frame Material : Polycarbonate

Ground Clips : Brass

Grounding : Self-Grounding

Overload UL20 Test : 100 cycles of OL at 4.8 times rated current

Strap Material : .046" Thick Galvanized Steel

Temperature Rise : Maximum 30° C Rise

Voltage : 120/277 VAC

Environmental Specifications

Flammability : Rated V-2 per UL 94

Operating Temperature : -40°C to 60°C

Product ID : Ratings are permanently marked on device

Terminal Accom. : Wiring Module

Terminal ID : Labeled on wiring module, switch is keyed to ensure proper installation

Termination : Modular

Mechanical Specifications

ANSI : C-73

Applicable Standards : UL20, CSA C22.2 No. 111

Certification/Listing : cULus (File #E7458)

Product ID : Ratings are permanently marked on device

RoHS : Compliant

Terminal Accom. : Wiring Module

Terminal ID : Labeled on wiring module, switch is keyed to ensure proper installation

Termination : Modular

Standards & Certifications

ANSI : C-73

Applicable Standards : UL20, CSA C22.2 No. 111

Brand : Lev-Lok Decora Plus

Certification/Listing : cULus (File #E7458)

Color : White

Device Type : Rocker Switch

Feature 2 : Illuminated - Load OFF

Function : Single-Pole

Grade : Heavy-Duty Industrial Specification Grade

RoHS : Compliant

Product Features

Brand : Lev-Lok Decora Plus

Color : White

Device Type : Rocker Switch

Feature 2 : Illuminated - Load OFF

Function : Single-Pole

Grade : Heavy-Duty Industrial Specification Grade

Patents*

CA2655707

US7666010

CA2667092

US8096818

US7357652

*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2021 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

