




Color :  Sea Spray

UPC Code : 078477807484

Country Of Origin : China

RoHS Compliant : Yes



Available Colors :



RUAA1-SE

Renu 3.6A USB Type-A/Type-A Wall Outlet Charger with 15A Tamper-Resistant Receptacle

Combination Duplex Receptacle/Outlet and USB Charger. 15 Amp, 125 Volt, Renu Tamper-Resistant Receptacle/Outlet, NEMA 5-15R. 3.6 Amps, 5VDC, 2.0 Type A USB Chargers. Grounding, Side Wired & Back Wired – Sea Spray

- **SMART** - Built-in smart chip recognizes the individual device's charging requirement to optimize the charge
- **POWERFUL** – Two high-powered charging ports with 3.6A of charging power
- **CONVENIENT** – No more searching for charging adapters! Upgrade your existing outlets so you can charge up to two USB powered electronics at once, leaving the outlets free for additional power needs
- **EASY** - Matte finish available in 20 popular colors that works with Leviton Renu wallplate REWP1/REWP2/REWP3/REWP4

Technical Information

Product Features

Amperage : 15 A

Brand : Renu

Color : Sea Spray

Color Change Kit : RKAA1

Device Type : USB Duplex Outlet

Grade : Residential

Grounding : Self-Grounding Clip and Green Ground Screw

Horsepower Rating : 15A-1/2 HP

NEMA : 5-15R

Ratings : 15A-125V

Type : Type A/A Duplex Receptacle

Voltage : 125 VAC

Wallplate : Not Included

Electrical Specifications

Amperage : 15 A

Flammability : Rated V-0 per UL 94

Grounding : Self-Grounding Clip and Green Ground Screw

Horsepower Rating : 15A-1/2 HP

Operating Temperature : -10°C to 40°C

Ratings : 15A-125V

Environmental Specifications

Body Material : Thermoplastic

Cover Material : Thermoplastic

Flammability : Rated V-0 per UL 94

Operating Temperature : -10°C to 40°C

Strap Material : Steel

Material Specifications

Body Material : Thermoplastic

Cover Material : Thermoplastic

Product ID : Stamped on Strap

Strap Material : Steel

Terminal Accom. : 14-12 AWG

Terminal ID : Brass-Hot Black-Hot White-Neutral Green-Gnd

Termination : Back & Side

Torque Range : 14 – 18 in.-lbs

Mechanical Specifications

Color : Sea Spray

Color Change Kit : RKAA1

Device Type : USB Duplex Outlet

Grade : Residential

NEMA : 5-15R

Product Family : Renu

Product ID : Stamped on Strap

Terminal Accom. : 14-12 AWG

Terminal ID : Brass-Hot Black-Hot White-Neutral Green-Gnd

Termination : Back & Side

Torque Range : 14 – 18 in.-lbs

Standards and Certifications

FCC Part 15 : Class B

Listed : cCSAus

NOM : 057

Warranty : 5-Year Limited

Features and Benefits



Wood Smoke

- Smart chip recognizes and optimizes the charging requirements of individual devices
- 3.6A charging capacity
- Two high-powered charging ports
- Two 15A or 20A Tamper-Resistant receptacles for improved safety
- USB ports are positioned vertically providing more space for maneuvering and reducing stress on USB cables
- Compatible with USB 2.0 devices
- Fits in a standard wallbox
- Back and side wired for easy installation
- Can replace existing outlets Can be multi-ganged with Renu devices
- Available in 20 popular colors to match any décor
- Once installed, face easily snaps OFF and ON. Change color by ordering the RKAA1 or RKAA2 color change kit
- Uses only Renu Wallplates (sold separately)

SPECIFICATION SUBMITTAL

JOB NAME: 	CATALOG NUMBERS: 	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2021 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts/

