

S332-S6



UPC Code: 07847767931

Country Of Origin: Slovakia

Item Description

32 Amp, 380-415 Volt, 3P+E (3P, 4W), Clock Position 6, IEC/EN 60309-1 & 60309-2, International Configuration Surface Mounting Socket Outlet, Industrial Grade, IP44, Splashproof - RED

Technical Information

Electrical Specifications

Amperage: 32 A

Frequency: 50/60Hz

Pole: 3

Voltage: 380-415 VAC

Wire: 4

Environmental Specifications

IK Rating: IK08

IP Rating: IP44

Operating Temperature: -25°C to 40°C

Material Specifications

Contacts: Nickel Plated Brass

Housing: Halogen-free engineering polymer

Mechanical Specifications

Terminal Accom.: 14-8 AWG

Product Features

Color: Red

Configuration: International

Device Type: Receptacle

Standards and Certifications

CE: Marked

IEC Rating: 60309-1 and 60309-2

NOM Certified: Yes

RETIE Certified: Yes

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

