

PLASTIC SCREWS / THUMB SCREWS

310 Series
Shoulder Screws

Specifications:

- Material: UL94 V-2 Nylon 6/6
- Color: Natural

Item No.	Thread	L		C		ØD		H		ØA		Hex Drive Size J	Bulk Pack Qty
		in		in		in		in		in			
31025025	#10-24	0.250		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025037	#10-24	0.375		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025050	#10-24	0.500		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025062	#10-24	0.625		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025075	#10-24	0.750		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025100	#10-24	1.000		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025125	#10-24	1.250		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025150	#10-24	1.500		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025175	#10-24	1.750		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025200	#10-24	2.000		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025225	#10-24	2.250		0.345 - 0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125 - 0.130	500
31025250	#10-24	2.500		0.375		0.238 - 0.248		0.177 - 0.188		0.357 - 0.375		0.125	500
31031025	1/4-20	0.250		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031031	1/4-20	0.312		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031037	1/4-20	0.375		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031050	1/4-20	0.500		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031062	1/4-20	0.625		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031075	1/4-20	0.750		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031100	1/4-20	1.000		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031150	1/4-20	1.500		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031175	1/4-20	1.750		0.408 - 0.438		0.301 - 0.311		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31031200	1/4-20	2.000		0.408 - 0.438		0.300 - 0.310		0.209 - 0.219		0.419 - 0.438		0.156 - 0.161	500
31037025	5/16-18	0.250		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	1000
31037037	5/16-18	0.375		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	500
31037050	5/16-18	0.500		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	500
31037062	5/16-18	0.625		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	500
31037075	5/16-18	0.750		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	500
31037100	5/16-18	1.000		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	500
31037125	5/16-18	1.250		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	500
31037150	5/16-18	1.500		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	250
31037175	5/16-18	1.750		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	250
31037200	5/16-18	2.000		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	250
31037225	5/16-18	2.250		0.470 - 0.500		0.363 - 0.373		0.240 - 0.250		0.543 - 0.562		0.188 - 0.193	250
31050037	3/8-16	0.375		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	500
31050050	3/8-16	0.500		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	500
31050062	3/8-16	0.625		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	500
31050075	3/8-16	0.750		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	500
31050100	3/8-16	1.000		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	500
31050125	3/8-16	1.250		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	500
31050150	3/8-16	1.500		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	250
31050175	3/8-16	1.750		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	250
31050200	3/8-16	2.000		0.595 - 0.625		0.488 - 0.498		0.302 - 0.312		0.729 - 0.750		0.250 - 0.255	250

09T Series
Knurled Head Thumb Screw

Specifications:

- Material: UL94 V-2 Nylon 6/6
- Color: Natural

Item No.	Thread	L		H		ØA	Bulk Pack Qty
		in		in			
090440018T	#4-40	0.188		0.280		0.300	500
090440025T	#4-40	0.250		0.280		0.300	500
090440037T	#4-40	0.375		0.280		0.300	1000
090440050T	#4-40	0.500		0.280		0.300	500
090440075T	#4-40	0.750		0.280		0.300	500
090632025T	#6-32	0.250		0.275		0.360	1000
090632037T	#6-32	0.375		0.275		0.360	1000
090632050T	#6-32	0.500		0.275		0.360	1000
090632075T	#6-32	0.750		0.275		0.360	500
090632100T	#6-32	1.000		0.275		0.360	500
090832018T	#8-32	0.188		0.305		0.425	500
090832025T	#8-32	0.250		0.305		0.425	500
090832037T	#8-32	0.375		0.305		0.425	500
090832050T	#8-32	0.500		0.305		0.425	1000
090832075T	#8-32	0.750		0.305		0.425	500
090832100T	#8-32	1.000		0.305		0.425	500
091024050T	#10-24	0.500		0.325		0.425	500
091024075T	#10-24	0.750		0.325		0.425	500
091024100T	#10-24	1.000		0.325		0.425	500
091024125T	#10-24	1.250		0.325		0.425	500
091024200T	#10-24	2.000		0.325		0.425	500
091032037T	#10-32	0.375		0.325		0.425	500
091032050T	#10-32	0.500		0.325		0.425	500
091032075T	#10-32	0.750		0.325		0.425	500

Item No.	Thread	L		H		ØA	Bulk Pack Qty
		in		in			
091032100T	#10-32	1.000		0.325		0.425	500
091032150T	#10-32	1.500		0.325		0.425	500
091032200T	#10-32	2.000		0.325		0.425	500
092520025T	1/4-20	0.250		0.365		0.540	500
092520037T	1/4-20	0.375		0.365		0.540	500
092520050T	1/4-20	0.500		0.365		0.540	1000
092520075T	1/4-20	0.750		0.365		0.540	1000
092520100T	1/4-20	1.000		0.365		0.540	1000
092520125T	1/4-20	1.250		0.365		0.540	500
092520150T	1/4-20	1.500		0.365		0.540	1000
0931218050T	5/16-18	0.500		0.385		0.615	500
0931218075T	5/16-18	0.750		0.385		0.615	500
0931218100T	5/16-18	1.000		0.385		0.615	500
0931218150T	5/16-18	1.500		0.385		0.615	500
0931218200T	5/16-18	2.000		0.385		0.615	500
0937516050T	3/8-16	0.500		0.430		0.687	500
0937516100T	3/8-16	1.000		0.430		0.687	500
0937516150T	3/8-16	1.500		0.430		0.687	250
0937516200T	3/8-16	2.000		0.430		0.687	250
0950013050T	1/2-13	0.500		0.468		0.750	250
0950013100T	1/2-13	1.000		0.468		0.750	500
0950013150T	1/2-13	1.500		0.468		0.750	250
0950013200T	1/2-13	2.000		0.468		0.750	500