


**Brass Compression Fittings
Branch Tees (OD Tube)**



Use with Copper, Brass, Aluminum or Plastic Tubing
(Plastic Tubing Requires Tubing Insert 295)
Three Piece Construction: Nut, Sleeve (or Ferrule) and Body
Meets SAE, ASA and ASME Specifications and Standards
Connection: OD Tube
Pressure Rating 500 PSI
Temperature Range: -65°F to 250°F

Part No.	Size (In)	A (In)	B (In)	C (In)
264X4	1/4	7/16-24UN	0.85"	1.28"
264X6	3/8	9/16-24UN	1"	1.42"
264X8	1/2	11/16-24UN	1.27"	1.87"

Part No.	Description	Material
1	Nut	Brass
2	Sleeve	Brass
3	Body	Brass

Drawing Date: 8/2019
Rev. Level-Date: R1 8/2021



WARNING: This product can expose you to chemicals, including lead, which is known to the State of California to cause cancer and reproductive harm. For more information go to www.P65Warnings.CA.gov