


Brass Compression Fittings
Male Union (OD Tube x MPT)



Use with Copper, Brass, Aluminum or Plastic Tubing
(Plastic Tubing Requires Tubing Insert 295)
Three Piece Construction: Nut, Sleeve (or Ferrule) and Body
Meets SAE, ASA and ASME Specifications and Standards
Connection: OD Tube x MPT
Pressure Rating 500 PSI
Temperature Range: -65°F to 250°F

Part No.	Size (In)	A (In)	B (In)	C (In)	D (In)	E (In)
268X2X2	1/8 x 1/8	1/8"	0.35"	0.87"	5/16-24UNF	7/16"
268X3X2	3/16 x 1/8	1/8"	0.35"	0.87"	3/8-24UNF	7/16"
268X4X2	1/4 x 1/8	1/8"	0.37"	0.87"	7/16-24UNF	7/16"
268X4X4	1/4 x 1/4	1/4"	0.47"	1.00"	7/16-24UNF	9/16"
268X4X6	1/4 x 3/8	3/8"	0.54"	1.09"	7/16-24UNF	11/16"
268X6X2	3/8 x 1/8	1/8"	0.37"	0.96"	9/16-24UNF	9/16"
268X6X4	3/8 x 1/4	1/4"	0.47"	1.04"	9/16-24UNF	9/16"
268X6X6	3/8 x 3/8	3/8"	0.47"	1.06"	9/16-24UNF	11/16"
268X8X4	1/2 x 1/4	1/4"	0.47"	1.12"	11/16-24UNF	11/16"
268X8X6	1/2 x 3/8	3/8"	0.49"	1.14"	11/16-24UNF	11/16"
268X8X8	1/2 x 1/2	1/2"	0.55"	1.26"	11/16-24UNF	7/8"
268X12X8	3/4 x 1/2	1/2"	0.55"	1.40"	1-18UNF	1"
268X12X12	3/4 x 3/4	3/4"	0.65"	1.52"	1-18UNF	1-1/16"

Part No.	Description	Material
1	Nut	Brass
2	Sleeve	Brass
3	Body	Brass

Drawing Date: 8/2019
Rev. Level-Date: R1 8/2021



WARNING: This product can expose you to chemicals, including lead, which is known to the State of California to cause cancer and reproductive harm. For more information go to www.P65Warnings.CA.gov