

Blow Guns

- Zinc Alloy Body (Delrin® Body ABG-01)
- Maximum Pressure: 150 psi
(Recommended Working Pressure 90-120 psi)
- Safety Tip Limits Air Pressure to 30 psi When Dead-Ended per OSHA Requirement (ABG-3020 and BG-3020)
- Max. 87 dBA



Includes One Rubber Tip
and One Safety Tip

Part No.
ABG-3020



Includes One Standard Tip
and One Safety Tip

Part No.
BG-3020



Lightweight Ergonomic
Design. 3" Nozzle Ideal
for Tight Spaces

Part No.
ABG-01-J

Connection Size
1/4" FPT

Pocket Tire Gauges



S410-C Tire Gauge



S510-M Tire Gauge



S458 Heavy-Duty Dual-Foot Tire Gauge

Part No.	Pressure Range	Increment	Head	Body	Bar (psi/kPa)
S410-C	10-50 psi	1 psi	Plastic	Metal	2-Sided Steel
S510-M-J	20-120 psi	2 psi	Metal	Metal	4-Sided Plastic
S458	10-120 psi	2 psi	Plastic	Metal	4-Sided Plastic

Inflators with Gauges

- Rugged Zinc Cast Body with Brass Internals for Long Life
- Built-In Air Relief Valve
- 6" Dual-Foot Air Chuck
- Easy to Read Pressure Bar 20 - 120 psi (STG-02)
- Easy to Read Built-In Sight Gauge 10 - 120 PSI (STG-06)
- Full Swivel Hose Fittings (STG-06)
- Protective Rubber Bumper (STG-06)
- Packaged for Retail Sales



Part No.
STG-02-J



Part No.
STG-06

Inlet
1/4" FPT

Pressure Range
10-120 psi

Increment
2 psi

Hose Length
12"