


# Outside Micrometer Economy Design

Item number: 103-176

## Images



## Description


Lightweight workshop design with baked-enamel-finished frame.

- Equipped with Ratchet Stop for constant measuring force.

## Features

|                                      |   |
|--------------------------------------|---|
| <b>Model:</b>                        | OM-1000   |
| <b>Digital/Analog:</b>               | Analog  |
| <b>Delivered:</b>                    | Including box, key, setting standard  |
| <b>Inch-Metric:</b>                  | Metric  |
| <b>Range:</b>                        | 975-1,000 mm  |
| <b>Graduation:</b>                   | 0,01 mm   |
| <b>Max. Permissible Error J MPE:</b> | $\pm 9 \mu\text{m}$   |
| <b>Flatness:</b>                     | $1 \mu\text{m}$   |
| <b>Parallelism:</b>                  | $12 \mu\text{m}$  |
| <b>Measuring face:</b>               | Carbide-tipped, micro-lap finish  |
| <b>Measuring spindle:</b>            | With spindle lock, $\varnothing 6,35 \text{ mm}$ ( $\leq 300 \text{ mm}$ ) $\varnothing 8 \text{ mm}$ ( $> 300 \text{ mm}$ ) , spindle pitch 0,5 mm |
| <b>Scale:</b>                        | Thimble and sleeve satin chrome finish, $\varnothing 21 \text{ mm}$   |
| <b>Measuring force:</b>              | 10 - 15 N   |
| <b>Mass:</b>                         | 8880 g  |

## Dimensions



## Accessories

Optional accessories:



## Micrometer Stand

for Micrometer 300-1000mm/12-40"

Art No. 156-103

Suggested retail price: 1,183.00 €\*  

---

Standard accessories:

---

## Micrometer Setting Standard

Length: 975mm

Art No. 167-139

Suggested retail price: 426.00 €\*  

---

