

Outside Micrometer Interchangeable Anvil

Item number: 104-171

Images



Description

This Outside Micrometer offers you an extra wide measuring range with the following benefits:

- Easy, interchangeable anvils allow a wide range of measurements.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	0 - 50 mm
Graduation:	0,01 mm
Limit of error:	$\pm 5 \mu\text{m}$
Delivered:	Including box, key, setting standard (1 pcs.), anvils (1 pcs.)
Spindle feed error:	$3 \mu\text{m}$
Flatness:	$0,6 \mu\text{m}$
Parallelism:	$2 \mu\text{m}$
Measuring face:	Carbide-tipped micro-lap finish spindle and hardened steel anvil
Measuring spindle:	With spindle lock, $\varnothing 6,35 \text{ mm}$ ($\leq 300 \text{ mm}$) $\varnothing 8 \text{ mm}$ ($> 300 \text{ mm}$), spindle pitch $0,5 \text{ mm}$
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$
Measuring force:	5 - 10 N
Setting standard:	1 (25 mm)
Interchangeable anvils:	1
Mass:	0.32 kg

Accessories

Standard accessories:

Micrometer Setting Standard



Length: 25mm

Art No. 167-101

Suggested retail price: 33.00 €*
