

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 1044AB-01

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Delivered:	With certificate of inspection, bezel clamp
Range:	5 mm
Range per rev.:	1 mm
Dial reading:	±0-100
Graduation:	0,01 mm
MPE first one revolution:	±10 µm
MPE first 2 1/2 revolutions:	±10 µm
MPE > 2 1/2-10 revolutions:	±13 µm
H MPE (Hysteresis):	3 µm
R MPE (Repeatability):	±3 µm
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,4 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application



Spindle Lifting Lever

for S-Type and A-Type Serie 1

Art No. 902100

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 15.00 €* *incl. VAT