

Dial Gauge, Flat Back, ISO Type

Item number: 1044AB-60

Images



Description

Compact Type 5 mm Range Small Diameter - Metric

This is a compact, dial indicator with a bezel \varnothing 40 mm. It offers you the following benefits:

- It is ideal for use in applications where space is limited.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	5 mm
Range per rev.:	1 mm
Dial reading:	$\pm 0-100$
Delivered:	With certificate of inspection
Graduation:	0.01 mm
MPE any 1/10 revolution:	5 μ m
MPE any 1/2 revolution:	9 μ m

MPE any 1 revolution:	10 µm
MPE measuring range:	12 µm
H MPE (Hysteresis):	3 µm
R MPE (Repeatability):	3 µm
Measuring force:	0,4-2 N
Stem:	8 mm
Contact point:	Carbide tipped, thread: M 2.5 x 0.45 mm
Continuous dial:	Yes
Type:	EN ISO Standard
Mass:	70 g

Dimensions

A: 32.5 mm
B: 57 mm
C: 40 mm
D: 15 mm
E: 20 mm
F: 12.2 mm
G: 24.8 mm
H: 38 mm
I: 6.6 mm

Accessories

Optional accessories:

Limit Hands (Green) 2 pcs.
Dial Indicator Series 1, Test Indicator
Art No. 21AAB363
Price on application

Bezel Clamp for Dial Gauge
Series 1
Art No. 21RZA149
Price on application

Spindle Lifting Lever

for S-Type and A-Type Serie 1

Art No. 902100

Price on application



Spare parts

Consumable spares:



Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 5.00 €*

NBR Rubber Boot

IP63 Series 1

Art No. 136838

Suggested retail price: 7.00 €*



NBR Rubber Boot

Digital Gauge ID-B, Dial Gauge IP63/IP64

Art No. 21AAB562

Suggested retail price: 7.00 €*

