

Outside Microm. Anvil Extension Collar

Item number: 105-103

Images



Description

This Outside Micrometer comes with Extension Anvil Collars.

It offers you the following benefits:

- The collars have a stable and rugged yet lightweight tube construction, and are ideal for large micrometers.
- The 50mm spindle stroke gives you extended range compared to standard spindle types.
- Anvil collars extend the measuring range even further.
- The setting standards supplied cover the whole measuring range.

Features

Model:	OMS1-600
Digital/Analog:	Analog
Delivered:	Including box, with spanner, setting standard (2 pcs.), 50 mm extension collar
Inch-Metric:	Metric
Measuring spindle:	With spindle lock, $\varnothing 8$ mm, spindle pitch 0,5 mm
Range:	500 - 600 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 21$ mm
Graduation:	0,01 mm

Limit of error:	±14 µm
Spindle feed error:	6 µm
Flatness:	1,3 µm
Parallelism:	8 µm
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5 - 10 N
Extension collar:	50 mm
Mass:	5.53 kg

Accessories

Standard accessories:



Micrometer Setting Standard
Length: 500mm
Art No. 167-120
Suggested retail price: 159.00 €*



Micrometer Setting Standard
Length: 550mm
Art No. 167-122
Suggested retail price: 176.00 €*
