

Outside Microm. Anvil Extension Collar

Item number: 105-107

Images



Description

This Outside Micrometer comes with Extension Anvil Collars.

It offers you the following benefits:

- The collars have a stable and rugged yet lightweight tube construction, and are ideal for large micrometers.
- The 50mm spindle stroke gives you extended range compared to standard spindle types.
- Anvil collars extend the measuring range even further.
- The setting standards supplied cover the whole measuring range.

Features

Model:	OMS1-1000
Digital/Analog:	Analog
Delivered:	Including box, with spanner, setting standard (2 pcs.), 50 mm extension collar
Inch-Metric:	Metric
Measuring spindle:	With spindle lock, $\varnothing 8$ mm, spindle pitch 0,5 mm
Range:	900 - 1,000 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 21$ mm
Graduation:	0,01 mm
Limit of error:	$\pm 20 \mu\text{m}$

Spindle feed error:	6 µm
Flatness:	1,3 µm
Parallelism:	12 µm
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5 - 10 N
Extension collar:	50 mm
Mass:	8.81 kg

Accessories

Standard accessories:

Micrometer Setting Standard

Length: 900mm
Art No. 167-136
Suggested retail price: 380.00 €*


Micrometer Setting Standard

Length: 950mm
Art No. 167-138
Suggested retail price: 415.00 €*

