


Measuring spindle:	With spindle lock, ø8 mm, spindle pitch 0,5 mm
Range:	1,500 - 1,600 mm
Scale:	Thimble and sleeve satin chrome finish, ø21 mm
Graduation:	0,01 mm
Limit of error:	±28 µm
Spindle feed error:	6 µm
Flatness:	1,3 µm
Parallelism:	18 µm
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5-10 N
Extension collar:	50 mm
Remarks:	With workpiece stop 100 mm adjustable
Mass:	12.5 kg

Dimensions



L: 1625 mm

a: 800 mm

Accessories

Standard accessories:

Micrometer Setting Standard

Length: 1500mm

Art No. 167-384

Suggested retail price: 867.00 €*



Micrometer Setting Standard

Length: 1550mm

Art No. 167-386

Suggested retail price: 893.00 €*

