

Outside Microm. Anvil Extension Collar

Item number: 105-419

Images



Description

This Outside Micrometer comes with Extension Anvil Collars.

It offers you the following benefits:


- The collars have a stable and rugged yet lightweight tube construction, and are ideal for large micrometers.
- The 50 mm spindle stroke gives you extended range compared to standard spindle types.
- Anvil collars extend the measuring range even further.
- The setting standards supplied cover the whole measuring range.

Features

| | |
|---------------------------|--|
| Model: | OMS2-1400P |
| Digital/Analog: | Analog |
| Delivered: | Including box, with spanner, setting standard (4 pcs.), 50/100 mm extension collar |
| Inch-Metric: | Metric |
| Measuring spindle: | With spindle lock, $\varnothing 8$ mm, spindle pitch 0,5 mm |
| Range: | 1,200/1,400 mm |
| Scale: | Thimble and sleeve satin chrome finish, $\varnothing 21$ mm |

| | |
|----------------------------|---------------------------------------|
| Graduation: | 0,01 mm |
| Limit of error: | ±25 µm |
| Spindle feed error: | 6 µm |
| Flatness: | 1,3 µm |
| Parallelism: | 16 µm |
| Measuring face: | Carbide-tipped, micro-lap finish |
| Measuring force: | 5-10 N |
| Extension collar: | 50/100 mm |
| Remarks: | With workpiece stop 100 mm adjustable |
| Mass: | 11.4 kg |

Dimensions



L: 1425 mm

a: 700 mm

Accessories

Standard accessories:

Micrometer Setting Standard

Length: 1200mm

Art No. 167-372

Suggested retail price: **670.00 €***



Micrometer Setting Standard

Length: 1250mm

Art No. 167-374

Suggested retail price: **709.00 €***



Micrometer Setting Standard

Length: 1300mm

Art No. 167-376

Suggested retail price: **740.00 €***



Micrometer Setting Standard

Length: 1350mm

Art No. 167-378

Suggested retail price: 759.00 €*

